

Plant Paging/Intercom Subset

By GAI-Tronics
Catalog # [845-008A300](#)

ICS / SP2 Remote Desktop Multi-party Subset, UL Safe area,
Black finish, 6' PVC handset cord



General

Color	Black
Material	ABS (Acrylonitrile butane styrene - Thermoplastic polymer)
Output Level Speaker	16 Ohm
Series	ICS
Signal Type	Analog
Type	Remote Desktop Subset
Weather Rating	NEMA Type 1

Dimensions

Cubic Capacity	309.82464 cu.in
Depth	4.56 in
Height	8.94 in
Weight	5 lb
Width	7.6 in

Certifications and Compliance

Certified Listed	UL
Hazardous Rating(s)	UL Safe Area

Product Assets

[Brochures - SP2 - VoIP Multicast Paging & Intercom Brochure](#)
[Installation Manuals - ICS - Page/Party® Desktop Subset](#)
[Literature - ICS Remote Stations](#)
[Literature - SP2 - Remote Handset Stations](#)

Related Products

[VoIP Plant Paging/Intercom Station](#)
[VoIP Plant Paging/Intercom Station](#)
[VoIP Plant Paging/Intercom Station](#)