

## Plant Paging/Intercom Subset

By GAI-Tronics  
Catalog # 845-008B300

ICS / SP2 Remote Desktop Multi-party Subset, CE Safe area,  
Black finish, 6' PVC handset cord



### General

Color	Black
Material	ABS (Acrylonitrile butane styrene - Thermoplastic polymer)
Output Level Speaker	16 Ohm
Power	2W
Series	ICS
	SP2
Signal Type	Analog
Type	Remote Desktop Subset
Weather Rating	NEMA Type 1

### Dimensions

Cubic Capacity	309.82464 cu.in
Depth	4.56 in
Height	8.94 in
Weight	5 lb
Width	7.6 in

### Electrical Ratings

Signal	N/A
--------	-----

### Certifications And Compliance

Certified Listed	CE
Hazardous Rating(s)	CE Safe Area

### Product Assets

[Brochures - SP2 - VoIP Multicast Paging & Intercom Brochure](#)  
[Installation Manuals - ICS - Page/Party® Desktop Subset](#)  
[Literature - SP2 - Remote Handset Stations](#)  
[Literature - ICS Remote Stations](#)