



Plant Paging/Intercom Subset

By GAI-Tronics
Catalog # [855-001A100](#)

ICS / SP2 Remote Flush-mount Multi-party Subset, UL Safe area, Orange finish, 6' PVC handset cord



General

Color	Orange
Material	Steel
Series	<ul style="list-style-type: none">• ICS• SP2
Signal Type	Analog
Type	Remote Flush-Mount Subset
Weather Rating	NEMA Type 1

Dimensions

Cubic Capacity	201.96 cu.in
Depth	5.61 in
Height	6 in
Weight	5 lb
Width	6 in

Certifications and Compliance

Certified Listed	UL
Hazardous Rating(s)	UL Safe Area

Product Assets

[Brochures - SP2 - VoIP Multicast Paging & Intercom Brochure](#)
[Installation Manuals - ICS - Page/Party® Flush-Mount Subset](#)
[Literature - ICS Remote Stations](#)
[Literature - SP2 - Remote Handset Stations](#)

Related Products

[VoIP Plant Paging/Intercom Station](#)
[VoIP Plant Paging/Intercom Station](#)
[VoIP Plant Paging/Intercom Station](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
GTC-855-001A100-SPEC-EN | REV 7/2023