



## Plant Paging/Intercom Subset

By GAI-Tronics  
Catalog # [855-001A1A0](#)

ICS / SP2 Remote Flush-mount Multi-party Subset, UL Safe area, Orange finish, 6' PVC handset cord, PCBA tropicalization



### General

Color	Orange
Material	Steel
Series	<ul style="list-style-type: none"><li>• ICS</li><li>• SP2</li></ul>
Signal Type	Analog
Type	Remote Flush-Mount Subset
Weather Rating	NEMA Type 1

### Dimensions

Cubic Capacity	201.96 cu.in
Depth	5.61 in
Height	6 in
Weight	5 lb
Width	6 in

### Certifications and Compliance

Certified Listed	UL
Hazardous Rating(s)	UL Safe Area

### Product Assets

[Brochures - SP2 - VoIP Multicast Paging & Intercom Brochure](#)  
[Installation Manuals - ICS - Page/Party® Flush-Mount Subset](#)  
[Literature - ICS Remote Stations](#)  
[Literature - SP2 - Remote Handset Stations](#)

### Related Products

[VoIP Plant Paging/Intercom Station](#)  
[VoIP Plant Paging/Intercom Station](#)  
[VoIP Plant Paging/Intercom Station](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
GTC-855-001A1A0-SPEC-EN | REV 7/2023