

Plant Paging/Intercom Subset

By GAI-Tronics
Catalog # 855-001A100

ICS / SP2 Remote Flush-mount Multi-party Subset, UL Safe area,
Orange finish, 6' PVC handset cord



General

Color	Orange
Material	Steel
Power	N/A
Series	ICS
	SP2
Signal Type	Analog
Type	Remote Flush-Mount Subset
Weather Rating	NEMA Type 1

Dimensions

Cubic Capacity	201.96 cu.in
Depth	5.61 in
Height	6 in
Weight	5 lb
Width	6 in

Electrical Ratings

Signal	N/A
--------	-----

Certifications And Compliance

Certified Listed	UL
Hazardous Rating(s)	UL Safe Area

Product Assets

[Brochures - SP2 - VoIP Multicast Paging & Intercom Brochure](#)
[Installation Manuals - ICS - Page/Party® Flush-Mount Subset](#)
[Literature - SP2 - Remote Handset Stations](#)
[Literature - ICS Remote Stations](#)