

# Flush-Mount Speaker

By GAI-Tronics  
 Catalog # [B650-8](#)

Flush-Mount ceiling speaker with enclosed rear chamber, ABS Construction, easy installation of back box with three mounting hooks; quick "spring clip" wire terminations

## Features

- 8 Ohm, 6W Speaker
- White ABS Grille and Enclosure
- Impedance or XFMR Version Available
- Three-way Easy Connect Terminals
- 50-15000 Hz. Frequency Range
- 90dB SPL @ 1 W, 1 Meter
- Dimensions: 9.5" (232mm) Dia. X 4 3/4" (120mm) D

## General

Catalog Number	B650-8
Mount location	Flush-Mount
Power	6W



## Dimensions

Depth	4.7
Diameter	9.1 in

## Electrical Ratings

Impedance	8 Ohms
Wattage	6 W

## Product Assets

- [Brochures - Loudspeaker Selection Guide](#)
- [Literature - Light & Industrial Speakers](#)
- [Specifications - B6508](#)
- [Wiring Diagrams - Remote Speaker Volume Control Assembly Outline & Wiring Diagram \(12506-001\)](#)