

25 Watt, 8 ohm ATEX Approved Speaker - Model DSP25EEXMN-8

By GAI-Tronics
Catalog # [DSP25EEXMN-8](#)



Non-Corrosive, Weatherproof, IP-66, 25 Watt Speaker in 8 Ohm

Features

- 25 Watt Speaker in 8 Ohm or 70/100V XFMR
- Non-Corrosive, Weatherproof, IP-66
- Anti-static Poly-amid Horn w/SS Bracket and Hardware
- 110/30 Degree Dispersion Angle @ 1000/4000 Hz.
- 9 3/4" (248mm) Dia x 13 3/8" (340mm) L
- Eex dem IIB+H2 T5 / 01 ATEX 235

General

Catalog Number	DSP25EEXMN-8
Color	Black
Material	Anti-Static Polyamide
Weather Rating	IP-66

Dimensions

Diameter	9.75 in
Length	13.375 in

Electrical Ratings

Wattage	25 W
---------	------

Certifications And Compliance

Hazardous Rating(s)	Eex dem IIB+H2 T5 / 01 ATEX 235
---------------------	---------------------------------

Product Assets

[Installation Manuals - Speaker/Horn Installation for GAI-TRONICS Communication Systems](#)
[Specifications - DSP25EEXMN8](#)