



## EZ Page Intercom, 230 VAC, CE certified

By GAI-Tronics  
Catalog # [GC-AC3](#)

EZ-Page is a common-talk communications system designed for a wide variety of rugged applications. The system is simple to use with push-to-talk / release-to-listen (PTT/RTL) operation.



### Features

- Master / Slave User Configurable
- Hands-free Operation
- Rugged Construction
- Wide Range of Operating Temperatures
- Easy Installation Power Lead and Single Audio Pair Only (Additional Pair Required for Master/ Slave)
- Compatible with GAI-TRONICS' [RigCom](#)
- Accepts Footswitch

### General

Color	RAL5017 Blue
Enclosure Type	Cast Aluminum
Series	EZ Page Intercom
Temperature Range	-40° F to +158° F
Weather Rating	IP 55

### Dimensions

Cubic Capacity	425.4488 cu.in
Depth	5.45
Height	11.2 in
Weight	10.93 lb
Width	6.97 in

### Electrical Ratings

Voltage Rating	207/256 VAC
----------------	-------------

### Certifications and Compliance

Certified Listed	CE
------------------	----

### Product Assets

[Installation Manuals - EZ Page Industrial Intercoms - Model GC-AC1, GC-DC1, and GC-AC2](#)  
[Literature - EZ Page Application Bulletin](#)  
[Literature - EZ Page Intercom - Product Literature](#)  
[Literature - EZ Page Intercom Sales Guide](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
GTC-GC-AC3-SPEC-EN | REV 7/2023