

EZ Page Intercom, 12-16 VDC Range

By GAI-Tronics
Catalog # GC-DC1

EZ-Page is a common-talk communications system designed for a wide variety of rugged applications. The system is simple to use with push-to-talk / release-to-listen (PTT/RTL) operation. For applications needing hands-free operation EZ Page is configurable for Master / Slave functionality.



Features

- Master / Slave User Configurable
- Hands-free Operation
- Rugged Construction
- Wide Range of Operating Temperatures
- Easy Installation Power Lead and Single Audio Pair Only (Additional Pair Required for Master/ Slave)
- Compatible with GAI-TRONICS' [RigCom](#)
- Accepts Footswitch

General

Color	RAL5017 Blue
Enclosure Type	Cast Aluminum
Series	EZ Page Intercom
Temperature Range	-40° F to +158° F

Dimensions

Cubic Capacity	419.3448 cu.in
Depth	5.45
Height	11.2 in
Weight	10 lb
Width	6.87 in

Electrical Ratings

Voltage Rating	12-16 VDC
----------------	-----------

Certifications And Compliance

Certified Listed	UL813
Nema Rating	NEMA 4X

Product Assets

[Installation Manuals - EZ Page Industrial Intercoms - Model GC-AC1, GC-DC1, and GC-AC2](#)

[Literature - EZ Page Application Bulletin](#)

[Literature - EZ Page Intercom Sales Guide](#)

[Literature - EZ Page Intercom - Product Literature](#)



A Hubbell brand