

HUBBCOM™ IP Devices - Flush-Mount, Hands-free

By GAI-Tronics
Catalog # [GSC4100](#)

HUBBCOM™ IP Devices has a multi-functional design that will provide solutions for all your communication needs. It provides the ability to combine web application control, VoIP SIP telephone operation, speaker broadcasts, and point-to-point server-less IP communication (audio and/or video).

Features

- Point-to-Point, Serverless Audio & Video
- Paging with Intercom (Soft Zoning, Multiple Conference Calls, Serverless)
- SIP Telephone
- Access Control
- Web Portal Access (applications)
- 7-inch Capacitive Touchscreen
- ONVIF-Compatible HD Camera
- Flush-mount/Wall-mount (Hands-free)
- Intuitive Operation
- 24 V dc or PoE / PoE+ Input
- Integral 2 W Speaker
- 8 Ohm, 8 W Speaker Output
- Two (2) Isolated Volt-free Outputs
- WiFi (802.11 a/b/g/n + MIMO)
- Bluetooth (Version 4.1 + CSA2 support / BLE)

Application

- Manufacturing Facilities
- Education
- Office Areas
- Security
- Production Offices
- Production Areas
- Healthcare
- Industrial Facilities
- Multi-Unit Residential



- Business Campuses
- Warehouses

General

Catalog Number	GSC4100
Connectivity Options	SIP, WiFi, Bluetooth Options
Mount location	Flush-Mount
Operating Temperature	0° C to 50° C
UPC	850025795388

Dimensions

Cubic Capacity	336 cu.in
Depth	2.8
Height	12 in
Weight	5 lb
Width	10 in

Product Assets

[Brochures - HUBBCOM™ Solutions Brochure - Communications & Control](#)
[Catalogs - Transportation - Rail Industry](#)
[Configuration Guide - HUBBCOM™ Device Configuration Manual](#)
[Installation Manuals - HUBBCOM™ Dual-Port Flush-Mount Smart Controllers](#)
[Installation Manuals - 42003-293C Kit Manual](#)
[Literature - HUBBCOM™ IP DEVICES](#)
[Software Downloads - HUBBCOM Firmware 3.12](#)
[Specifications - GSC4100](#)