

Security Speaker - (8 Ohm)

By GAI-Tronics
Catalog # [SAFE15-8](#)

15 Watt Vandal-proof Speaker, Non-Corrosive, Weatherproof, IP67. Impedance or XFMR Version Available w/Six Voltage Power Taps. Available in Aluminum Alloy, Red or White.160/55 Degree Dispersion Angle @ 1000/4000 Hz.

Features

- 15 Watt
- Impedance or XFMR Version Available w/Six Voltage Power Taps
- Non-Corrosive, Weatherproof, IP-67
- 160/55 Degree Dispersion Angle @ 1000/4000 Hz.
- Dimensions: 8 1/4" (210mm) x 4 1/8" (105mm) W x 2 3/8" (59mm) D

General

Catalog Number	SAFE15-8
Color	White
Material	Aluminum

Dimensions



Diameter	2.375 in
Height	8.25 in
Weight	3.74 lb
Width	4.125 in

Electrical Ratings

Wattage	15 W
---------	------

Certifications And Compliance

Compliance	IP67
------------	------

Product Assets

[Brochures - Loudspeaker Selection Guide](#)
[Specifications - SAFE158](#)