



Indoor/Outdoor Compression Driver - 13314 Series (70V ohm)

By GAI-Tronics
Catalog # [13314-003](#)

A compression drivers that is designed to provide optimum performance in both commercial and industrial applications. These indoor/outdoor compression drivers are commonly used in light and heavy manufacturing facilities with high ambient noise, and corrosive and hazardous environments.

Features

- Low Distortion, Superior Sound
- Rain-Tight, Chemical Resistant Housing
- Suitable for Harsh or Corrosive Environments
- Variable Impedance Drivers
- Fits GAI-TRONICS' Horns with 1 3/8" - 18 UNEF Threads
- NEMA 4X

General

| | |
|-----------------------|--------------------------------------|
| Operating Temperature | -40° C to +70° C (-40° F to +158° F) |
| UPC | 850025795197 |

Dimensions

| | |
|--------|--------|
| Weight | 3.4 lb |
|--------|--------|



Electrical Ratings

| | |
|-----------|-----|
| Impedance | 70V |
|-----------|-----|

Certifications and Compliance

| | |
|---------------------|--|
| Hazardous Rating(s) | <ul style="list-style-type: none">• Class I, Div. 2, Groups A, B, C, D• Class II, Div. 2, Groups F, G• Class III, Div. 2 |
| Nema Rating | 4X |

Product Assets

- [Installation Manuals - Speaker/Horn Installation for GAI-TRONICS Communication Systems](#)
- [Installation Manuals - Model 13314-003 Div. 2 Hazardous Area 70-Volt Horn Driver](#)
- [Literature - Indoor / Outdoor Compression Driver](#)



A proud member of the Hubbell Family.