



* Representative image

Bracket

by ANDERSON
Catalog ID: GWB1R

Bracket, Ductile Iron, for supporting ground wire suspension clamp, trunnion style.

Product Details

General

Bolt Installation Torque (Recommended)	0 ft-lbs
Material - Clamp	Ductile Iron
Material - Hardware	Galvanized Steel
Number of Bolt Holes	0
Product Category	Bracket
Strength Rating - Ultimate Body	5000 lb
UPC	096359314035

Dimensions

Actual Clamp Strand Diameter Range	0 in
Assembly Rating (Ultimate)	0 lb
Clamping - Maximum	0 in
Clamping - Minimum	0 in
Clevis Opening	0 in
Diameter - Bolt	0 in
Diameter - Clamping Hardware	0 in
Diameter - Clevis Pin	0 in
Diameter - Lag Screw - Maximum	0.5 in
Diameter - Mounting Bolt - Maximum	0.63 in
Diameter - Pin	0 in
Length - Pin	0 in
Mounting Bolt Spacing	3.25 in
Nominal Guy Wire Size	0 in
Weight	2.940 lb

Conductor Related

Conductor Diameter - Maximum	0 in
------------------------------	------