



Heater, 1500W, Single Phase, 208-240V

By HOT BOX
Catalog # ACI1500-208/240



1500W, 208-240V, single phase heater w/ thermostat & fan

*Representative Image

Features

- Better Freeze Protection - Heater is thermostatically controlled to maintain an interior temperature of 40 degrees F to protect equipment from external temperatures as low as -30 degrees F in accordance with ASSE 1060 1.2.2.1.
- Better Performance and Safety - Wall-mounted design elevates heater above discharge point.
- Fast and Easy Installation - 6' power cord and plug.
- Quiet Operation - Factor lubricated 100 cfm fan.

General

Description - Heater	208-240V single phase heater w/ thermostat & fan
Material	Steel

Dimensions

Dimensions	20 in x 5 in x 5 in
Height	5 in
Length	20 in
Weight	12 lb
Width	5 in

Electrical Ratings

Wattage - Heater	1500 W
------------------	--------

Product Assets

[Catalogs - Hot Box Enclosures HB-20 \(CA07145E\)](#)
[Literature - HOT BOX® Aluminum Drop Over Enclosures \(SF07127E\)](#)
[Sales Drawings - Specification-Heater Standard 120v,208v-240v](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
HBOX-ACI1500-208/240-SPEC-EN | REV 1/2024