

EARTHTAGS

Brass, Brass Nickel Plated or Stainless Steel


General Information

- Provides an earth bond attachment for a cable gland.
- Manufactured in Brass, Brass Nickel Plated and Stainless Steel
- Stainless Steel earthtags are available, but the dimensions may differ slightly to those stated in the selection table. Please contact Hawke Sales Team for details.
- The earthtags shape may vary for different sizes.

Selection Table					
Thread Type	Gland Size 'V'	'W'	'X'	'Y'	ʻZ'
	M16	36.6	30	6.75	1.5
	M20	39.6	33	6.75	1.5
	M25	45.5	36.5	6.85	1.5
	M32	53.5	42.5	12.6	1.5
	M40	59.6	44	13.4	1.5
	M50	78.9	58	13.5	1.5
	M63	87.6	67	13.5	1.5
Metric	M75	93.7	73	13.5	1.5
	M80	128	88	14	1.5
	M90	128	85	14	1.5
	M100	128	104	14	2
	M110	136	115	13.5	2
	M115	141	120	13.5	2
	M120	143.5	122.5	13.5	2
	M130	153	128	13.5	2
	1/2"	39.6	33	6.75	1.5
	3/4"	45.5	36.5	6.85	1.5
	1"	53.5	42.5	12.6	1.5
	1 1/4"	59.6	44	13.4	1.5
NDT	1 1/2"	78.9	58	13.5	1.5
NPT	2"	87.6	67	13.5	1.5
	2 1/2"	93.7	73	13.5	1.5
	3"	128	85	13.5	1.5
	3 1/2"	128	104	14	1.5
	4"	144	120	14	2

Note: All dimensions are in millimetres, except NPT sizes

 $Other {\it sizes may be available on request. Please contact Hawke for more details.}$



Ordering Example:					
If brass is required please omit material selection Format for ordering is as follows:					
Product	Thread Size	Material			
ET	M25	NP			

Please note all NPT entries should be state as a decimal




LOCKNUTS

Brass, Brass Nickel Plated or Stainless Steel

General Information

- For use on cable gland entry threads.
- Manufactured in Brass, Brass Nickel Plated and Stainless Steel
- Stainless Steel locknuts are also available, but dimensions may differ from the ones in the table.
- Locknuts for PG thread sizes are available.



Selection Table							
Gland Size	Across Flats 'X'	Across Corners 'Y'	'Z'	NPT * Gland Size	Across Flats 'X'	Across Corners 'Y'	ʻZ'
M16	22	24	3.7/4.7	-	_	-	_
M20	24	26.4	3.7/4.7	1/2"	27	29.7	3.0/4.0
M25	30	33.3	3.7/4.7	3/4"	30.5	33.5	3.7/4.7
M32	40	44	3.7/4.7	1"	36	39.5	6.0/7.0
M40	46	50.5	4.5/5.5	1 1/4"	46	50.5	6.0/7.0
M50	65	71.5	4.5/5.5	1 ½"	55	60.6	6.0/7.0
M63	80	88	6.0/7.0	2"	65	70.8	6.0/7.0
M75	90	99	6.5/7.5	2 1/2"	80	90	6.0/7.0
M80	107	122.2	9.5/10.5	3"	95	107	6.0/7.0
M90	107	122.2	9.5/10.5	3 ½"	128	143	8.5/9.5
M100	128	147	9.5/10.5	4"	128	143	8.5/9.5
M110	128	147	9.5/10.5	5"	170	187	9.5/10.5
M115	128	147	9.5/10.5	6"	200	220	9.5/10.5
M120	140	152	9.5/10.5				
M130	150	165	9.5/10.5				

Note: All dimensions are in millimetres except where * denotes dimensions in inches.

Ordering Example:					
If brass is required please omit material selection					
Product	Thread Size	Material			
LN	M25	NP			

Please note all NPT entries should be state as a decimal





HHI-HKE-Mult-EARTHTAGS-LOCKNUTS-SPEC-UK-2022-00314