



PVC Shrouds

For Hawke Cable Glands



Shrouds for fitting over cable glands when required by the application. Suitable for indoor and outdoor use.

Technical Data	
Material	PVC
Colour	Black
Operating Temperature	-60 to +90 degC
UV Resistance	Excellent (Tested to ASTM G 154-12a / ASTM D 412-2006)

Size Selection		501/321														All other Hawke Gland Types							
Shroud Size	Internal Diameter 'A'	Length 'B'	Os M16	Os M20/O	A	B	C	C2	D	E	F	2K	Os/O	A	B	C	C2	D	E	F			
Size 1B	21.0	27.0	■									■											
Size 2B	25.5	75.0		■									■										
Size 3B	31.5	77.0			■									■									
Size 4B	39.0	83.0				■									■								
Size 5B	50.0	89.0					■									■							
Size 6B	60	97						■									■						
Size 7B	70	123							■									■					
Size 8B	87.5	120								■									■				
Size 9B	103.5	130									■									■			

Shrouds for gland sizes G,H & J available on request

Ordering Information	
Product	Size
SHR	4B

Part code example - SHR4B