

8100/8100W

Cable Rack

■ The Model 8100 High Voltage Cable Rack provides a user with 125 feet of High Voltage Cable and 125 feet of Ground Cable. Used in conjunction with most cable fault locators (Thumpers) and HVC Couplers, the 8100 provide a convenient and flexible device to safely and quickly make connections to cables under test. The High Voltage cable is terminated with an MC connector to allow for either a locking plier connection or another accessory such as those listed on the back of this sheet. The ground cable is terminated with a standard grounding clamp which can be used with a shotgun stick. A pigtail is available to retrofit most thumpers to this cable rack system or our HVC series of couplers. Please consult your representative for further details.



FEATURES

- ☑ **125 Feet** of High Voltage Cable
- ☑ **125 Feet** of Ground Cable
- ☑ **High Voltage** Cable Reel
- ☑ **Ground** Cable Reel
- ☑ **Female MC** High Voltage Connector
- ☑ **Mounting Rack** for Cable Reels
- ☑ **Two Wheel** Hand Truck for 8100W

BENEFITS

Female MC Connector – for easy connection of HV couplers and thumpers

HV Output Cable – rated for voltages of 70kV DC

Ground Cable – flexible welding cable with safety grounding lugs every 10 feet

TECHNICAL SPECIFICATIONS

General

High Voltage Cable	125 feet (38m)	Rated for 70kV DC
Ground Cable	125 feet (38m)	4 gage 600V welding cable

Weights and Dimensions

17"W x 17"D x 35"H (43 x 43 x 89cm) Unit weight, 82lbs (37kg), Shipping weight, 175lbs (80kg)

ACCESSORIES

- Catalog number 8530, Elbow Adapter
- Catalog number 8526, Bushing Adapter
- Catalog number 8527, Bushing Adapter
- Catalog number 8540, Locking plier

ORDERING INFORMATION

System

Cable Rack	8100
Cable Rack with Wheels	8100W
Pig Tail Output Cable	8100PT

ADAPTERS

