



* Representative image

Compression Stirrup

by ANDERSON
Catalog ID: HLS80040P

Aluminum Overhead Compression Stirrup

- Protects primary lines from arcing damage. Wide stance gives good stability for installing hotline clamp.

Product Details

General

Bolt Installation Torque (Recommended)	0 ft-lbs
Compression Tool Type	1-1/2
Material - Bail	Copper
Material - Body	Aluminum Alloy
Material - Stirrup	Copper
Plating	No
Type	Stirrups
UPC	096359316541

Dimensions

Copper Loop Size	0.46 in
Diameter - Stirrup Nominal Wire	4/0 Solid
Height	3.750 in
Weight	1.176 lb
Width - Main Contact	4 in

Conductor Related

Conductor Diameter - Maximum	1.04 in
Conductor Diameter - Minimum	0.93 in
Conductor Diameter Range	0.93 - 1.04
Conductor Type	Aluminum

Logistics

Packaging Type	Bag
----------------	-----

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscs@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com