

## HS21009

Wall Bracket

Incandescent



HS21009-09	Brushed Nickel
HS21009-15	Chrome
HS21009-125	Bronze

**Dimension:** 24" w (A), 8" ht. (B). Extends 7 1/2" (C)

**Description:** 3-Lt. Wall Bracket. Mount in "up" or "down" position.

**Backplate:** Oval Shape: 9-3/8" tall x 4-5/8" wide.

**Glass:** Etched glass shade: 5-1/2" dia. x 4-7/8" tall. (HS99003-01)

**Application:** Indoor

**Approvals:** UL/CUL Damp location listed.

**Installation:** Fits standard Outlet Box

**Lamps:** 3 Medium Base lamps, at 60 watts max. (Not Included)

**Electrical:** 120V, 60 Hz

