

Description:

7" Integrated LED Surface Mount Light, 24-Pack

Specifications:

- Diffuse White Polycarbonate Round
- Dimmable to 10% brightness (See Dimming Notes)
- Fixture covers a standard 4" recessed outlet box
- Screws included
- 6 in of wire supplied
- Americans With Disabilities Act (ADA) compliant

Performance:

Number of Modules	1
Input Power	15.8 W
Input Voltage	120 VAC
Input Frequency	60 Hz
Lumens/LPW (Delivered)	1,050/66.4 (LM-79)
CCT	3000 K
CRI	90 CRI
Life (hours)	35000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15, Class B
Warranty	1-year Limited Warranty
Labels	cULus Damp Location Listed Meets California Title 24 JA8-2019

HS32001-28-30-Q24

**Dimensions:**

Width: 7-3/4 in
Diameter: 7-3/4 in
Height: 1 in

Diffuse White Polycarbonate Round
Width: 5-1/16 in
Height: 11/16 in

Dimming Notes:

HS32001-28-30-Q24

HS32001-28-30-Q24 is designed to be compatible with many Triac/Forward Phase controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls:

Leviton 6674

Lutron Caseta Wireless

Lutron MACL-153M

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered