

15kV Cold Shrink Termination with Stem Connector

By Hubbell Power Systems
Catalog # [15TZ2JA24](#)

Cold Shrink Termination, 15kV, Cable Insulation Diameter Range = 0.710 - 1.260 inches, 2/0 Solid or Compact and 1/0 Stranded or Compressed, Stem Connector



General

Connector Type	Stem Connector
Type	15kV Outdoor Termination
UPC	096359746027

Dimensions

Cable Insulation Diameter Maximum	1.260 in
Cable Insulation Diameter Minimum	0.710 in
Weight	0.825 lb

Electrical Ratings

AC Withstand Voltage (1 min)	34 kV
Basic Impulse Level	110 kV
Corona Extinction (3pC)	11 kV
kV Class	15 kV

Conductor Related

Cable Insulation Diameter Range	0.710 - 1.260
Solid or Compact Conductor	2/0
Stranded or Compressed Conductor	1/0

Logistics

Pallet Quantity	162
Standard Package	3

Product Assets

[Installation Manuals - ISTZ15J1-J2](#)
[Installation Manuals - TD391E_ISTZ15J1-J2](#)
[Literature - Crimp Chart \(ISTWLUGA\)](#)
[Literature - Cold Shrink Termination Kits \(SF03062E\)](#)
[Sales Drawings - 15TZ](#)
[Video - Grease Best Practices \(HPS_CA_UTL_VI_EN_00030\)](#)