

15kV Cold Shrink Termination with Stem Connector

By Hubbell Power Systems
Catalog # [15TZ3JA27](#)

Cold Shrink Termination, 15kV, Cable Insulation Diameter Range = 0.830 - 1.340 inches, 250 Compact and 4/0 Stranded or Compressed, Stem Connector



General

Connector Type	Stem Connector
Type	15kV Outdoor Termination
UPC	096359736264

Dimensions

Cable Insulation Diameter Maximum	1.340 in
Cable Insulation Diameter Minimum	0.830 in
Weight	0.825 lb

Electrical Ratings

AC Withstand Voltage (1 min)	34 kV
Basic Impulse Level	110 kV
Corona Extinction (3pC)	11 kV
kV Class	15 kV

Conductor Related

Cable Insulation Diameter Range	0.830 - 1.340
Solid or Compacted Conductor	250
Stranded or Compressed Conductor	4/0

Logistics

Pallet Quantity	162
Standard Package	3

Product Assets

[Installation Manuals - ISTZ15J3-J4](#)
[Installation Manuals - TD397E_ISTZ15J3-J4](#)
[Literature - Crimp Chart \(ISTWLUGA\)](#)
[Literature - Cold Shrink Termination Kits \(SF03062E\)](#)
[Sales Drawings - 15TZ](#)
[Video - Grease Best PRactices \(HPS_CA_UTL_VI_EN_00030\)](#)