

## Crimp Connectors, Bimetal

By Hubbell Power Systems  
Catalog # 200LUGB3

Crimp connector, 200A BI-METAL #2 STR



### Features

- Meets or Exceeds IEEE Std. 386 and IEEE Std. 592 requirements
- Interchangeable with other products meeting the same requirements
- Fully shielded, insulated and submersible

### General

Accessory Type	Crimp Connectors
Connector Type	Bimetal
EU RoHS Indicator	No
PROBELOK® Connectors	No
Type	Tools / Lugs / Parts
UPC	096359392231

### Dimensions

Weight	0.100 lb
--------	----------

### Electrical Ratings

Current Rating	200 A
----------------	-------

### Conductor Related

Solid or Compacted Conductor	#1
Stranded or Compressed Conductor	#2

### Logistics

Standard Package	25
------------------	----

### Product Assets

- [Catalogs - Cable Accessories \(C7\)](#)
- [Installation Manuals - Recommended Crimp Tools and Dies for 200A Elbow Bi-Metal Connectors \(IS-200LUGB\)](#)
- [Sales Drawings - 200 AMP, 15/25 KV Long, Bimetal Connector\(200LUGBX\)](#)
- [Video - Grease Best Practices \(HPS\\_CA\\_UTL\\_VI\\_EN\\_00030\)](#)