

2-Position Junction W/ Bracket, 15kV

By Hubbell Power Systems
Catalog # [215J2B](#)



Load Break Junction, 2-Position, 200 Amp, 15 kV, Bracket

Features

- Meets or Exceeds IEEE Std. 386 and IEEE Std. 592 requirements
- Interchangeable with other products meeting the same requirements
- Fully shielded, insulated and submersible

General

EU RoHS Indicator	No
Mounting Type	Brackets
Number of Positions	2
Type	200Amp Load Break
UPC	096359391333

Dimensions

Weight	8.250 lb
--------	----------

Electrical Ratings

AC Withstand Voltage (1 min)	34 kV
Basic Impulse Level	95 kV
Corona Extinction (3pC)	11 kV
Current Rating	200 A
kV Class	15 kV

Logistics

Pallet Quantity	32
Standard Package	1

Product Assets

[Catalogs - Cable Accessories \(C7\)](#)
[Installation Manuals - 15kV & 25/28kV 200 Amp Junctions \(IS-200JCT\)](#)
[Sales Drawings - 200A 15kV JUNCTION \(215JXB\)](#)
[SDS - VERSILUBE G661 SILICONE COMPOUND](#)
[Test Documents - ANSI/IEEE Design Test Report - 15kV 200A Loadbreak Separable Connectors \(G11-12-01\)](#)
[Video - 200A Loadbreak Elbow Fault Closure \(VI03045E\)](#)
[Video - Grease Best PRactices \(HPS_CA_UTL_VI_EN_00030\)](#)