

25/28 kV Load Break Feed-Thru Bushing Insert

By Hubbell Power Systems
Catalog # [228FTI](#)



Load Break Feed-Thru Bushing Insert, 200 Amp, 25/28 kV.

Features

- Meets or Exceeds IEEE Std. 386 and IEEE Std. 592 requirements
- Interchangeable with other products meeting the same requirements
- Fully shielded, insulated and submersible

General

Type 200Amp Load Break
UPC 096359639169

Dimensions

Dimensions 10.00 in x 7.00 in x 4.00 in
Height 4.00 in
Length 10.00 in
Weight 7.080 lb
Width 7.00 in

Electrical Ratings

AC Withstand Voltage (1 min)	40 kV
Basic Impulse Level	125 kV
Corona Extinction (3pC)	19 kV
Current Rating	200 A
kV Class	25/28 kV

Logistics

Pallet Quantity	108
Standard Package	1

Product Assets

[Catalogs - Cable Accessories \(C7\)](#)
[Installation Manuals - IS-200FTI_Rev_A_Oct_2016](#)
[Installation Manuals - 15kV & 25kV 200 Amp Feed-thru Inserts](#)
[Installation and Operating Instructions \(IS-200FTI\)](#)
[Sales Drawings - 228FTI](#)
[SDS - VERSILUBE G661 SILICONE COMPOUND](#)
[Video - 200A Loadbreak Elbow Fault Closure \(VI03045E\)](#)
[Video - Grease Best PRactices \(HPS_CA_UTL_VI_EN_00030\)](#)