

# 28kV Cold Shrink Termination with Stem Connector

By Hubbell Power Systems  
Catalog # [28TZ3JA27](#)

Cold Shrink Termination, 28kV, Cable Insulation Diameter Range = 0.830 - 1.340 inches, 250 Compact and 4/0 Stranded or Compressed, Stem Connector



\*Representative Image

### General

Connector Type	Stem Connector
Type	28kV Outdoor Termination

### Dimensions

Cable Insulation Diameter Maximum	1.340 in
Cable Insulation Diameter Minimum	0.830 in
Weight	0.825 lb

### Electrical Ratings

AC Withstand Voltage (1 min)	45 kV
Basic Impulse Level	165 kV
Corona Extinction (3pC)	21.5 kV
kV Class	28 kV

### Conductor Related

Cable Insulation Diameter Range	0.830 - 1.340
Solid or Compacted Conductor	250
Stranded or Compressed Conductor	4/0

### Logistics

Pallet Quantity	800
Standard Package	3

### Product Assets

- [Installation Manuals - ISTZ28J3-J4](#)
- [Installation Manuals - TD398E\\_ISTZ28J3-J4](#)
- [Literature - Crimp Chart \(ISTWLUGA\)](#)
- [Literature - Cold Shrink Termination Kits \(SF03062E\)](#)
- [Sales Drawings - 28TZ](#)
- [Video - Grease Best PRactices \(HPS\\_CA\\_UTL\\_VI\\_EN\\_00030\)](#)

