

## 15 kV Elbow Tap Plug Kit with Test Point and Shield Adapter Kit

By Hubbell Power Systems  
Catalog # [615ETPF22TS](#)

15 kV 600 Amp Elbow Tap Plug Kit with Test Point. Cable insulation range 0.640 in - 0.820 in. Kit includes T-body, insulating plug with cap, compression lug, threaded stud, cable adapter, and shield adapter kit



\*Representative Image

### Features

- Meets or Exceeds IEEE Std. 386 and IEEE Std. 592 requirements
- Interchangeable with other products meeting the same requirements
- Fully shielded, insulated and submersible
- Optional features include test point, shear bolt connector, cold shrink jacket seal kit or shield adapter kit

### General

Connector Type	Aluminum
Type	600Amp Dead Break
With Seal Kit	Yes
With Test Point	Yes

### Dimensions

Weight	9.150 lb
--------	----------

### Electrical Ratings

AC Withstand Voltage (1 min)	34 kV
Basic Impulse Level	95 kV
Corona Extinction (3pC)	11 kV
Current Rating	200 A
kV Class	15 kV

### Conductor Related

Solid or Compacted Conductor	#1
Stranded or Compressed Conductor	#2

### Logistics

Standard Package	1
------------------	---

### Product Assets

[Catalogs - Cable Accessories \(C7\)](#)  
[Test Documents - Cable Accessories Test Report - 15kV & 25kV 600A \(CH-9904\)](#)  
[Video - Grease Best PRactices \(HPS\\_CA\\_UTL\\_VI\\_EN\\_00030\)](#)

### Related Products

[BTW1575F12](#)