

## 15 kV, 600 Amp ETP Kit w/ Test Point and Seal Kit

By Hubbell Power Systems  
Catalog # [615ETPK27TJ](#)



\*Representative Image

15 kV 600 Amp Elbow Tap Plug Kit with Test Point. Cable insulation range 1.090 in - 1.310 in. Kit includes T-body, insulating plug with cap, compression lug, threaded stud, and cable adapter

### Features

- Meets or Exceeds IEEE Std. 386 and IEEE Std. 592 requirements
- Interchangeable with other products meeting the same requirements
- Fully shielded, insulated and submersible
- Optional features include test point, shear bolt connector, cold shrink jacket seal kit or shield adapter kit

### General

Connector Type	Aluminum
Type	600 Amp Dead Break
With Seal Kit	Yes
With Test Point	Yes

### Dimensions

Weight	9.150 lb
--------	----------

### Electrical Ratings

AC Withstand Voltage (1 min)	34 kV
Basic Impulse Level	95 kV
Corona Extinction (3pC)	11 kV
Current Rating	600 A
kV Class	15 kV

### Conductor Related

Solid or Compacted Conductor	250
Stranded or Compressed Conductor	4/0

### Logistics

Standard Package	1
------------------	---

### Product Assets

[Catalogs - Cable Accessories \(C7\)](#)  
[Installation Manuals - Deadbreak Connector 600A, 15/25kV Class T-Body \(IS-600BT\)](#)  
[Installation Manuals - Recommended Crimp Tools and Dies for 600A T-Body Connectors \(IS-600LUG\)](#)  
[Installation Manuals - Loadbreak Elbow Tap Plug \(IS-600ETP\)](#)  
[SDS - VERSILUBE G661 SILICONE COMPOUND](#)  
[Test Documents - Cable Accessories Test Report - 15kV & 25kV 600A \(CH-9904\)](#)  
[Video - Grease Best PRactices \(HPS\\_CA\\_UTL\\_VI\\_EN\\_00030\)](#)

### Related Products

[BTW1575F12](#)  
[BTW1575F12](#)