

15 kV, 600 Amp ETP Kit

By Hubbell Power Systems
Catalog # [615ETPL30](#)

15 kV 600 Amp Elbow Tap Plug Kit. Cable insulation range 1.180 in - 1.465 in. Kit includes T-body, insulating plug with cap, compression lug, threaded stud, and cable adapter



*Representative Image

Features

- Meets or Exceeds IEEE Std. 386 and IEEE Std. 592 requirements
- Interchangeable with other products meeting the same requirements
- Fully shielded, insulated and submersible
- Optional features include test point, shear bolt connector, cold shrink jacket seal kit or shield adapter kit

General

Connector Type	Aluminum
Type	600 Amp Dead Break
With Seal Kit	No
With Test Point	No

Dimensions

Weight	8.650 lb
--------	----------

Electrical Ratings

AC Withstand Voltage (1 min)	34 kV
Basic Impulse Level	95 kV
Corona Extinction (3pC)	11 kV
Current Rating	600 A
kV Class	15 kV

Conductor Related

Solid or Compacted Conductor	400
Stranded or Compressed Conductor	350

Logistics

Pallet Quantity	64
Standard Package	1

Product Assets

[Catalogs - Cable Accessories \(C7\)](#)
[Installation Manuals - Deadbreak Connector 600A, 15/25kV Class T-Body \(IS-600BT\)](#)
[Installation Manuals - Recommended Crimp Tools and Dies for 600A T-Body Connectors \(IS-600LUG\)](#)
[Installation Manuals - Loadbreak Elbow Tap Plug \(IS-600ETP\)](#)
[SDS - VERSILUBE G661 SILICONE COMPOUND](#)
[Test Documents - Cable Accessories Test Report - 15kV & 25kV 600A \(CH-9904\)](#)
[Video - Grease Best PRactices \(HPS_CA_UTL_VI_EN_00030\)](#)

Related Products

[BTW1575F12](#)
[BTW1575F12](#)