

15 kV, 600 Amp ETP Kit

By Hubbell Power Systems
Catalog # [615ETPN40](#)

15 kV 600 Amp Elbow Tap Plug Kit. Cable insulation range 1.515 in - 1.780 in. Kit includes T-body, insulating plug with cap, compression lug, threaded stud, and cable adapter



*Representative Image

Features

- Meets or Exceeds IEEE Std. 386 and IEEE Std. 592 requirements
- Interchangeable with other products meeting the same requirements
- Fully shielded, insulated and submersible
- Optional features include test point, shear bolt connector, cold shrink jacket seal kit or shield adapter kit

General

| | |
|-----------------|--------------------|
| Connector Type | Aluminum |
| Type | 600 Amp Dead Break |
| With Seal Kit | No |
| With Test Point | No |

Dimensions

| | |
|--------|----------|
| Weight | 8.650 lb |
|--------|----------|

Electrical Ratings

| | |
|------------------------------|-------|
| AC Withstand Voltage (1 min) | 34 kV |
| Basic Impulse Level | 95 kV |
| Corona Extinction (3pC) | 11 kV |
| Current Rating | 600 A |
| kV Class | 15 kV |

Conductor Related

| | |
|----------------------------------|------|
| Solid or Compacted Conductor | 1000 |
| Stranded or Compressed Conductor | 900 |

Logistics

| | |
|------------------|---|
| Standard Package | 1 |
|------------------|---|

Product Assets

[Catalogs - Cable Accessories \(C7\)](#)
[Installation Manuals - Deadbreak Connector 600A, 15/25kV Class T-Body \(IS-600BT\)](#)
[Installation Manuals - Recommended Crimp Tools and Dies for 600A T-Body Connectors \(IS-600LUG\)](#)
[Installation Manuals - Loadbreak Elbow Tap Plug \(IS-600ETP\)](#)
[SDS - VERSILUBE G661 SILICONE COMPOUND](#)
[Test Documents - Cable Accessories Test Report - 15kV & 25kV 600A \(CH-9904\)](#)
[Video - Grease Best PRactices \(HPS_CA_UTL_VI_EN_00030\)](#)

Related Products

[BTW1575F12](#)
[BTW1575F12](#)