

15 kV LRTP Kit w/ Jacket Seal Kit

By Hubbell Power Systems
Catalog # 615LRTPN39J

15 kV 600 Amp Load Break Reducing Tap Plug Kit. Cable insulation range 1.515 in - 1.780 in. Kit includes T-body, insulating plug with cap, compression lug, threaded stud, and cable adapter



*Representative Image

Features

- Meets or Exceeds IEEE Std. 386 and IEEE Std. 592 requirements
- Interchangeable with other products meeting the same requirements
- Fully shielded, insulated and submersible
- Optional features include test point, shear bolt connector, cold shrink jacket seal kit or shield adapter kit

General

Connector Type	Aluminum Threaded
Type	600 Amp Dead Break
With Seal Kit	Yes
With Test Point	No

Dimensions

Weight	10.000 lb
--------	-----------

Electrical Ratings

AC Withstand Voltage (1 min)	34 kV
Basic Impulse Level	95 kV
Corona Extinction (3pC)	11 kV
Current Rating	600 A
kV Class	15 kV

Conductor Related

Stranded or Compressed Conductor	800
----------------------------------	-----

Logistics

Standard Package	1
------------------	---

Product Assets

[Catalogs - Cable Accessories \(C7\)](#)

[SDS - VERSILUBE G661 SILICONE COMPOUND](#)

[Test Documents - Cable Accessories Test Report - 15kV & 25kV 600A \(CH-9904\)](#)

[Video - Grease Best PRactices \(HPS_CA_UTL_VI_EN_00030\)](#)

Related Products

[BTW1575F12](#)

[BTW1575F12](#)