

25/28 kV, 600 Amp, T-Body Kit w/ shield adapter kit,

By Hubbell Power Systems
Catalog # [625BTLM39S](#)

25/28 kV 600 Amp T-Body Kit. Cable insulation range 1.280 in - 1.430 in. Kit includes T-body, insulating plug with cap, compression lug, threaded stud, cable adapter, and shield adapter kit



*Representative Image

Features

- Meets or Exceeds IEEE Std. 386 and IEEE Std. 592 requirements
- Interchangeable with other products meeting the same requirements
- Fully shielded, insulated and submersible
- Optional features include test point, shear bolt connector, cold shrink jacket seal kit or shield adapter kit

General

Connector Type	Aluminum
Type	600Amp Dead Break
With Seal Kit	Yes
With Test Point	No

Dimensions

Weight	8.650 lb
--------	----------

Electrical Ratings

AC Withstand Voltage (1 min)	45 kV
Basic Impulse Level	125 kV
Corona Extinction (3pC)	19 kV
Current Rating	600 A
kV Class	25/28 kV

Conductor Related

Stranded or Compressed Conductor	800
----------------------------------	-----

Logistics

Standard Package	1
------------------	---

Product Assets

[Catalogs - Cable Accessories \(C7\)](#)

[Sales Drawings - 25/28 kV Deadbreak Elbow Kit \(625BTWXX\)](#)

[Test Documents - Cable Accessories Test Report - 15kV & 25kV 600A \(CH-9904\)](#)

[Video - Grease Best PRactices \(HPS_CA_UTL_VI_EN_00030\)](#)

Related Products

[BTW1575F12](#)

[BTW1575F12](#)