

25/28 kV, 600 Amp ETP Kit w/ Seal Kit

By Hubbell Power Systems
Catalog # [625ETPH27J](#)

25/28 kV 600 Amp Elbow Tap Plug Kit. Cable insulation range 0.850 in - 1.050 in. Kit includes T-body, insulating plug with cap, compression lug, threaded stud, and cable adapter



*Representative Image

Features

- Meets or Exceeds IEEE Std. 386 and IEEE Std. 592 requirements
- Interchangeable with other products meeting the same requirements
- Fully shielded, insulated and submersible
- Optional features include test point, shear bolt connector, cold shrink jacket seal kit or shield adapter kit

General

| | |
|-----------------|--------------------|
| Connector Type | Aluminum |
| Type | 600 Amp Dead Break |
| With Seal Kit | Yes |
| With Test Point | No |

Dimensions

| | |
|--------|----------|
| Weight | 9.150 lb |
|--------|----------|

Electrical Ratings

| | |
|------------------------------|----------|
| AC Withstand Voltage (1 min) | 45 kV |
| Basic Impulse Level | 125 kV |
| Corona Extinction (3pC) | 21 kV |
| Current Rating | 600 A |
| kV Class | 25/28 kV |

Conductor Related

| | |
|----------------------------------|-----|
| Solid or Compacted Conductor | 250 |
| Stranded or Compressed Conductor | 4/0 |

Logistics

| | |
|------------------|---|
| Standard Package | 1 |
|------------------|---|

Product Assets

[Catalogs - Cable Accessories \(C7\)](#)
[Test Documents - Cable Accessories Test Report - 15kV & 25kV 600A \(CH-9904\)](#)
[Video - Grease Best PRactices \(HPS_CA_UTL_VI_EN_00030\)](#)

Related Products

[BTW1575F12](#)
[BTW1575F12](#)