

## 25/28 kV Elbow Tap Plug Kit, with Shield Adapter Kit

By Hubbell Power Systems  
Catalog # [625ETPJ26S](#)

25/28 kV 600 Amp Elbow Tap Plug Kit. Cable insulation range 0.980 in - 1.180 in. Kit includes T-body, insulating plug with cap, compression lug, threaded stud, cable adapter, and shield adapter kit



\*Representative Image

### Features

- Meets or Exceeds IEEE Std. 386 and IEEE Std. 592 requirements
- Interchangeable with other products meeting the same requirements
- Fully shielded, insulated and submersible
- Optional features include test point, shear bolt connector, cold shrink jacket seal kit or shield adapter kit

### General

|                 |                   |
|-----------------|-------------------|
| Connector Type  | Aluminum          |
| Type            | 600Amp Dead Break |
| With Seal Kit   | Yes               |
| With Test Point | No                |

### Dimensions

|        |          |
|--------|----------|
| Weight | 9.150 lb |
|--------|----------|

### Electrical Ratings

|                              |          |
|------------------------------|----------|
| AC Withstand Voltage (1 min) | 40 kV    |
| Basic Impulse Level          | 125 kV   |
| Corona Extinction (3pC)      | 19 kV    |
| Current Rating               | 200 A    |
| kV Class                     | 25/28 kV |

### Conductor Related

|                                  |     |
|----------------------------------|-----|
| Solid or Compacted Conductor     | 4/0 |
| Stranded or Compressed Conductor | 3/0 |

### Logistics

|                  |   |
|------------------|---|
| Standard Package | 1 |
|------------------|---|

### Product Assets

[Catalogs - Cable Accessories \(C7\)](#)  
[Test Documents - Cable Accessories Test Report - 15kV & 25kV 600A \(CH-9904\)](#)  
[Video - Grease Best PRactices \(HPS\\_CA\\_UTL\\_VI\\_EN\\_00030\)](#)

### Related Products

[BTW1575F12](#)  
[BTW1575F12](#)