

## 25/28 kV, 600 Amp ETP Kit w/ Seal Kit

By Hubbell Power Systems  
Catalog # [625ETPM31J](#)

25/28 kV 600 Amp Elbow Tap Plug Kit. Cable insulation range 1.370 in - 1.630 in. Kit includes T-body, insulating plug with cap, compression lug, threaded stud, and cable adapter



\*Representative Image

### Features

- Meets or Exceeds IEEE Std. 386 and IEEE Std. 592 requirements
- Interchangeable with other products meeting the same requirements
- Fully shielded, insulated and submersible
- Optional features include test point, shear bolt connector, cold shrink jacket seal kit or shield adapter kit

### General

Connector Type	Aluminum
Type	600 Amp Dead Break
With Seal Kit	Yes
With Test Point	No

### Dimensions

Weight	9.150 lb
--------	----------

### Electrical Ratings

AC Withstand Voltage (1 min)	45 kV
Basic Impulse Level	125 kV
Corona Extinction (3pC)	21 kV
Current Rating	600 A
kV Class	25/28 kV

### Conductor Related

Solid or Compacted Conductor	450
Stranded or Compressed Conductor	400

### Logistics

Standard Package	1
------------------	---

### Product Assets

[Catalogs - Cable Accessories \(C7\)](#)  
[Test Documents - Cable Accessories Test Report - 15kV & 25kV 600A \(CH-9904\)](#)  
[Video - Grease Best PRactices \(HPS\\_CA\\_UTL\\_VI\\_EN\\_00030\)](#)

### Related Products

[BTW1575F12](#)  
[BTW1575F12](#)