

25/28kV Elbow Tap Plug W/ Stud

By Hubbell Power Systems
Catalog # [625ETPS](#)

25/28 kV 600/200 Amp Elbow Tap Plug with Stud.



*Representative Image

Features

- Meets or Exceeds IEEE Std. 386 and IEEE Std. 592 requirements
- Interchangeable with other products meeting the same requirements
- Fully shielded, insulated and submersible

General

EU RoHS Indicator	No
Type	Plugs
UPC	096359393177

Dimensions

Dimensions	9.00 in x 6.00 in x 4.000 in
Height	4.000 in
Length	9.00 in
Weight	2.150 lb
Width	6.00 in

Electrical Ratings

AC Withstand Voltage (1 min)	45 kV
Basic Impulse Level	125 kV
Corona Extinction (3pC)	21 kV
Current Rating	600 A
kV Class	25/28 kV

Logistics

Pallet Quantity	176
Standard Package	1

Product Assets

- [Catalogs - Cable Accessories \(C7\)](#)
- [Sales Drawings - Elbow Tap Plug 25 kV \(026388-00\)](#)
- [SDS - VERSILUBE G661 SILICONE COMPOUND](#)
- [Test Documents - Cable Accessories Test Report - 15kV & 25kV 600A \(CH-9904\)](#)
- [Video - Grease Best PRactices \(HPS_CA_UTL_VI_EN_00030\)](#)