

## 600A Insulating Cap

By Hubbell Power Systems  
Catalog # [625IC](#)

25/28 kV 600 Amp Insulating Cap with Stud.



\*Representative Image

### Features

- Meets or Exceeds IEEE Std. 386 and IEEE Std. 592 requirements
- Interchangeable with other products meeting the same requirements
- Fully shielded, insulated and submersible

### General

EU RoHS Indicator	No
Type	600 Amp Dead Break
UPC	096359393191

### Dimensions

Dimensions	9.00 in x 6.00 in x 4.000 in
Height	4.000 in
Length	9.00 in
Weight	1.800 lb
Width	6.00 in

### Electrical Ratings

AC Withstand Voltage (1 min)	45 kV
Basic Impulse Level	125 kV
Corona Extinction (3pC)	21 kV
Current Rating	600 A
kV Class	15 kV

### Logistics

Standard Package	1
------------------	---

### Product Assets

[Catalogs - Cable Accessories \(C7\)](#)  
[Installation Manuals - Deadbreak Connector 15/25kV, 600A Insulating Cap \(IS-600IC\)](#)  
[Sales Drawings - 625IC\\_3\\_](#)  
[SDS - VERSILUBE G661 SILICONE COMPOUND](#)  
[Test Documents - Cable Accessories Test Report - 15kV & 25kV 600A \(CH-9904\)](#)  
[Video - Grease Best Practices \(HPS\\_CA\\_UTL\\_VI\\_EN\\_00030\)](#)