

25/28 kV 600 Amp 3-pt Junction Bracket.

By Hubbell Power Systems
Catalog # [625J3B](#)



25/28 kV 600 Amp 3-pt Junction Bracket.

Features

- Meets or Exceeds IEEE Std. 386 and IEEE Std. 592 requirements
- Interchangeable with other products meeting the same requirements
- Fully shielded, insulated and submersible

General

EU RoHS Indicator	No
Mounting Type	Brackets
Number of Positions	3
Type	600 Amp Dead Break
UPC	096359393252

Dimensions

Weight	12.750 lb
--------	-----------

Electrical Ratings

AC Withstand Voltage (1 min)	40 kV
Basic Impulse Level	125 kV
Corona Extinction (3pC)	19 kV
Current Rating	600 A
kV Class	25/28 kV;15 kV

Logistics

Pallet Quantity	25
Standard Package	1

Product Assets

[Catalogs - Cable Accessories \(C7\)](#)
[Installation Manuals - 600A Deadbreak Junction \(IS-600JCT\)](#)
[Sales Drawings - JUNCTIONS, 25/28KV 600A \(625JXB\)](#)
[SDS - VERSILUBE G661 SILICONE COMPOUND](#)
[Test Documents - Cable Accessories Test Report - 15kV & 25kV 600A \(CH-9904\)](#)
[Video - Grease Best PRactices \(HPS_CA_UTL_VI_EN_00030\)](#)