

25/28 kV LRTP Kit w/ Shield Adapter Kit

By Hubbell Power Systems
Catalog # [625LRTPG26S](#)

25/28 kV 600 Amp Load Break Reducing Tap Plug Kit. Cable insulation range 0.760 in - 0.950 in. Kit includes T-body, insulating plug with cap, compression lug, threaded stud, cable adapter, and shield adapter kit



*Representative Image

Features

- Meets or Exceeds IEEE Std. 386 and IEEE Std. 592 requirements
- Interchangeable with other products meeting the same requirements
- Fully shielded, insulated and submersible
- Optional features include test point, shear bolt connector, cold shrink jacket seal kit or shield adapter kit

General

Connector Type	Aluminum Threaded
Type	600Amp Dead Break
With Seal Kit	Yes
With Test Point	No

Dimensions

Weight	10.000 lb
--------	-----------

Electrical Ratings

AC Withstand Voltage (1 min)	40 kV
Basic Impulse Level	125 kV
Corona Extinction (3pC)	19 kV
Current Rating	200 A
kV Class	25/28 kV

Conductor Related

Solid or Compacted Conductor	4/0
Stranded or Compressed Conductor	3/0

Logistics

Standard Package	1
------------------	---

Product Assets

- [Catalogs - Cable Accessories \(C7\)](#)
- [Test Documents - Cable Accessories Test Report - 15kV & 25kV 600A \(CH-9904\)](#)
- [Video - Grease Best PRactices \(HPS_CA_UTL_VI_EN_00030\)](#)

Related Products

- [BTW1575F12](#)
- [BTW1575F12](#)