

## 25/28 kV LRTP Kit w/ Test Point

By Hubbell Power Systems  
Catalog # [625LRTP35T](#)

25/28 kV 600 Amp Load Break Reducing Tap Plug Kit with Test Point. Cable insulation range 1.180 in - 1.465 in. Kit includes T-body, insulating plug with cap, compression lug, threaded stud, and cable adapter



\*Representative Image

### Features

- Meets or Exceeds IEEE Std. 386 and IEEE Std. 592 requirements
- Interchangeable with other products meeting the same requirements
- Fully shielded, insulated and submersible
- Optional features include test point, shear bolt connector, cold shrink jacket seal kit or shield adapter kit

### General

Connector Type	Aluminum Threaded
Type	600 Amp Dead Break
With Seal Kit	No
With Test Point	Yes

### Dimensions

Weight	9.500 lb
--------	----------

### Electrical Ratings

AC Withstand Voltage (1 min)	45 kV
Basic Impulse Level	125 kV
Corona Extinction (3pC)	21 kV
Current Rating	600 A
kV Class	25/28 kV

### Conductor Related

Solid or Compacted Conductor	700
Stranded or Compressed Conductor	600

### Logistics

Standard Package	1
------------------	---

### Product Assets

- [Catalogs - Cable Accessories \(C7\)](#)
- [Test Documents - Cable Accessories Test Report - 15kV & 25kV 600A \(CH-9904\)](#)
- [Video - Grease Best PRactices \(HPS\\_CA\\_UTL\\_VI\\_EN\\_00030\)](#)

### Related Products

- [BTW1575F12](#)
- [BTW1575F12](#)