

25/28 kV LRTP Kit with Test Point and Shield Adapter Kit

By Hubbell Power Systems
Catalog # [625LRTPM30TS](#)

25/28 kV 600 Amp Load Break Reducing Tap Plug Kit with Test Point. Cable insulation range 1.370 in - 1.630 in. Kit includes T-body, insulating plug with cap, compression lug, threaded stud, cable adapter, and shield adapter kit



*Representative Image

Features

- Meets or Exceeds IEEE Std. 386 and IEEE Std. 592 requirements
- Interchangeable with other products meeting the same requirements
- Fully shielded, insulated and submersible
- Optional features include test point, shear bolt connector, cold shrink jacket seal kit or shield adapter kit

General

| | |
|-----------------|-------------------|
| Connector Type | Aluminum Threaded |
| Type | 600Amp Dead Break |
| With Seal Kit | Yes |
| With Test Point | Yes |

Dimensions

| | |
|--------|-----------|
| Weight | 10.000 lb |
|--------|-----------|

Electrical Ratings

| | |
|------------------------------|----------|
| AC Withstand Voltage (1 min) | 40 kV |
| Basic Impulse Level | 125 kV |
| Corona Extinction (3pC) | 19 kV |
| Current Rating | 200 A |
| kV Class | 25/28 kV |

Conductor Related

| | |
|----------------------------------|-----|
| Solid or Compacted Conductor | 400 |
| Stranded or Compressed Conductor | 350 |

Logistics

| | |
|------------------|---|
| Standard Package | 1 |
|------------------|---|

Product Assets

[Catalogs - Cable Accessories \(C7\)](#)

[Test Documents - Cable Accessories Test Report - 15kV & 25kV 600A \(CH-9904\)](#)

[Video - Grease Best PRactices \(HPS_CA_UTL_VI_EN_00030\)](#)

Related Products

[BTW1575F12](#)

[BTW1575F12](#)