

BI-Metal Threaded

By Hubbell Power Systems
Catalog # [625LUGB24T](#)

BI-Metal Threaded Lug, 600A, Conductor Range = 1/0
Stranded or Compressed and 2/0 Compact or Solid



Features

- Meets or Exceeds IEEE Std. 386 and IEEE Std. 592 requirements
- Interchangeable with other products meeting the same requirements
- Fully shielded, insulated and submersible

General

Connector Type BI-Metal Threaded
Type 600Amp DeadBreak

Dimensions

Weight 1.25 lb

Electrical Ratings

Current Rating 600 A

Conductor Related

Solid or Compacted 2/0
Conductor
Stranded or Compressed 1/0
Conductor

Logistics

Standard Package 3

Product Assets

[Video - Grease Best Practices \(HPS_CA_UTL_VI_EN_00030\)](#)