

TapMaster Junction, Mounting Brackets, 5 positions

By Hubbell Power Systems
Catalog # [628TM22222B](#)



TapMaster Junction 5-PT BRACKET 28KV

Features

- Meets or Exceeds IEEE Std. 386 and IEEE Std. 592 requirements
- Interchangeable with other products meeting the same requirements
- Fully shielded, insulated and submersible

General

EU RoHS Indicator	No
Mounting Type	Brackets
Number of Positions	5
Type	600 Amp Dead Break
UPC	096359665670

Dimensions

Weight	26.000 lb
--------	-----------

Electrical Ratings

AC Withstand Voltage (1 min)	45 kV
Basic Impulse Level	125 kV
Corona Extinction (3pC)	21 kV
Current Rating	600 A
kV Class	15 kV;25/28 kV

Logistics

Standard Package	1
------------------	---

Product Assets

[Catalogs - Cable Accessories \(C7\)](#)
[Sales Drawings - 628TM22222B Drawing](#)
[SDS - VERSILUBE G661 SILICONE COMPOUND](#)
[Test Documents - Cable Accessories Test Report - 15kV & 25kV 600A \(CH-9904\)](#)
[Video - Grease Best Practices \(HPS_CA_UTL_VI_EN_00030\)](#)