

TapMaster Junction, Mounting U-Straps, 5 positions

By Hubbell Power Systems
Catalog # [628TM2222U](#)



TapMaster Junction 5-PT U-STRAPS

Features

- Meets or Exceeds IEEE Std. 386 and IEEE Std. 592 requirements
- Interchangeable with other products meeting the same requirements
- Fully shielded, insulated and submersible

General

EU RoHS Indicator	No
Mounting Type	U-Straps
Number of Positions	5
Type	600 Amp Dead Break
UPC	096359649441

Dimensions

Dimensions	20.00 in x 6.00 in x 5.00 in
Height	5.00 in
Length	20.00 in
Weight	20.000 lb
Width	6.00 in

Electrical Ratings

AC Withstand Voltage (1 min)	45 kV
Basic Impulse Level	125 kV
Corona Extinction (3pC)	21 kV
Current Rating	600 A
kV Class	15 kV;25/28 kV

Logistics

Standard Package	1
------------------	---

Product Assets

[Catalogs - Cable Accessories \(C7\)](#)
[Sales Drawings - 628TM2222U Drawing](#)
[SDS - VERSILUBE G661 SILICONE COMPOUND](#)
[Test Documents - Cable Accessories Test Report - 15kV & 25kV 600A \(CH-9904\)](#)
[Video - Grease Best Practices \(HPS_CA_UTL_VI_EN_00030\)](#)