

**TapMaster Junction, Mounting U-Straps, 3 positions**

By Hubbell Power Systems  
Catalog # [628TM626U](#)

TapMaster Junction 3-PT U-STRAPS 25KV



**Features**

- Meets or Exceeds IEEE Std. 386 and IEEE Std. 592 requirements
- Interchangeable with other products meeting the same requirements
- Fully shielded, insulated and submersible

**General**

EU RoHS Indicator	No
Mounting Type	U-Straps
Number of Positions	3
Type	600 Amp Dead Break
UPC	096359656999

**Dimensions**

Weight	20.300 lb
--------	-----------

**Electrical Ratings**

AC Withstand Voltage (1 min)	45 kV
Basic Impulse Level	125 kV
Corona Extinction (3pC)	21 kV
Current Rating	600 A
kV Class	15 kV;25/28 kV

**Logistics**

Standard Package	1
------------------	---

**Product Assets**

[Catalogs - Cable Accessories \(C7\)](#)  
[Sales Drawings - 628TM626U Drawing](#)  
[SDS - VERSILUBE G661 SILICONE COMPOUND](#)  
[Test Documents - Cable Accessories Test Report - 15kV & 25kV 600A \(CH-9904\)](#)  
[Video - Grease Best PRactices \(HPS\\_CA\\_UTL\\_VI\\_EN\\_00030\)](#)