

## 35kV t-body kit

By Hubbell Power Systems  
Catalog # [635BTJ24TS](#)

35kV 600A T-Body Kit, with Test Point, Cable Insulation Diameter Range = 1.160 - 1.305 Inches. Kit includes T-body with Testpoint, Cable Adapter, Aluminum Stud, Insulating Plug with Cap, Shield Adapter Kit, and Compression connector for 1/0 Stranded or Compressed and 2/0 Solid or Compact conductor.



### Features

- Meets or Exceeds IEEE Std. 386 and IEEE Std. 592 requirements
- Interchangeable with other products meeting the same requirements
- Fully shielded, insulated and submersible
- Optional features include test point, shear bolt connector, cold shrink jacket seal kit or shield adapter kit

### General

Connector Type	Aluminum
Type	Deadbreak T-Body Kit
UPC	096359737292
With Seal Kit	No
With Test Point	Yes

### Electrical Ratings

AC Withstand Voltage (1 min)	50 kV
Basic Impulse Level	125 kV
Corona Extinction (3pC)	26 kV
Current Rating	600 A
kV Class	35 kV

### Conductor Related

Solid or Compacted Conductor	2/0
Stranded or Compressed Conductor	1/0

### Logistics

Standard Package	1
------------------	---

### Product Assets

[Catalogs - Cable Accessories \(C7\)](#)  
[Installation Manuals - IS635BT Installation & Operating Instructions \(TD03052E\\_IS635BT\)](#)  
[Sales Drawings - 35 kV Deadbreak Elbow Kit \(635BTwxx\)](#)  
[Test Documents - 35kV Class 600 Deadbreak Connector Test Report](#)  
[Video - Grease Best PRactices \(HPS\\_CA\\_UTL\\_VI\\_EN\\_00030\)](#)

### Related Products

[BTW1575F12](#)  
[BTW1575F12](#)