

T-Body Deadbreak Elbows

By Hubbell Power Systems
Catalog # [635TBT](#)

35kV 600/900A T-body With Test Point



Features

- Meets or Exceeds IEEE Std. 386 and IEEE Std. 592 requirements
- Interchangeable with other products meeting the same requirements
- Fully shielded, insulated and submersible
- Optional features include test point, shear bolt connector, cold shrink jacket seal kit or shield adapter kit

General

| | |
|-----------------|------------------|
| Type | Deadbreak T-Body |
| UPC | 096359685371 |
| With Seal Kit | No |
| With Test Point | Yes |

Dimensions

| | |
|------------|---------------------------------|
| Dimensions | 15.000 in x 9.000 in x 4.750 in |
| Height | 4.750 in |
| Length | 15.000 in |
| Weight | 4.75 lb |
| Width | 9.000 in |

Electrical Ratings

| | |
|------------------------------|--------|
| AC Withstand Voltage (1 min) | 50 kV |
| Basic Impulse Level | 200 kV |
| Corona Extinction (3pC) | 26 kV |
| Current Rating | 600 A |
| kV Class | 35 kV |

Logistics

| | |
|------------------|---|
| Carton Quantity | 9 |
| Standard Package | 1 |

Product Assets

[Catalogs - Cable Accessories \(C7\)](#)

[Sales Drawings - 635TBx](#)

[Video - Grease Best Practices \(HPS_CA_UTL_VI_EN_00030\)](#)