

2" Square Shaft Extension(SS200), 10ft

By Hubbell Power Systems
Catalog # C1100566

SS200, 10' (3048 mm) ft long with no helix



Features

- Finish: Galvanized
- Capacity of helical pile can be determined by measuring installation
- Bolt and nut are assembled to extension at the factory

Application

Helical Anchoring

General

| | |
|-------------------|--|
| Coating | Galvanized, ASTM A-153 |
| EU RoHS Indicator | No |
| Strength Note | Ultimate strength ratings apply to properly installed anchors only. Failure to install within 5 ° of alignment with the guy load may significantly lower strength. |
| Tensile Strength | 150000 lb. |
| Torque Rating | 16000 ft-lbs |
| Type | Anchor Extensions |
| UPC | 096359243298 |

Dimensions

| | |
|------------|----------------------------------|
| Dimensions | 123.000 in x 3.250 in x 5.000 in |
| Height | 5.000 in |
| Length | 123.000 in |
| Weight | 147.412 lb |
| Width | 3.250 in |

Logistics

| | |
|------------------|----|
| Pallet Quantity | 12 |
| Standard Package | 1 |

Product Assets

[Brochures - CHANCE® Foundation Solutions Helical Deep Foundation Products Brochure \(BR04146E\)](#)
[Catalogs - CHANCE Helical Solutions Product Catalog \(CA04140E\)](#)
[Catalogs - Anchors \(4\)](#)
[ISO Certificates - HUS ISO 9001_2015 Cert Jan, 2023](#)
[Literature - Square Shaft Efficient Helical Pile Design \(BR04326E\)](#)
[Literature - New Construction Helical Pile Foundation System \(SF04215E_0419\)](#)
[Sales Drawings - SS200 Anchors \(SA11010019\)](#)
[SDS - MSDS - Galvanized Steel Products](#)
[Video - CHANCE Square Shaft Anchor Tools Selection Process \(VI0651E\)](#)
[Video - CHANCE Square Shaft Anchor Installation \(VI0655E\)](#)

Related Products

[P0010030P](#)
[P0011445P](#)