

2" Square Shaft Lead (SS200), 8/10/12/14 x 10ft

By Hubbell Power Systems
Catalog # [C1100573](#)

SS200, 10' long with 8",10",12",14" helices



Features

- Finish: Galvanized
- Capacity of helical pile can be determined by measuring installation

Application

Helical Anchoring

General

Coating	Galvanized, ASTM A-153
EU RoHS Indicator	No
Number of Helices	4
Strength Note	Ultimate strength ratings apply to properly installed anchors only. Failure to install within 5 ° of alignment with the guy load may significantly lower strength.
Tensile Strength	150000 lb.
Torque Rating	16000 ft-lbs
Type	Lead Sections
UPC	096359010005

Dimensions

Anchor Helix Diameter(s)	8 in - 10 in - 12 in - 14 in
Length	122.000 in
Weight	209.063 lb

Logistics

Pallet Quantity	12
Standard Package	1

Product Assets

[Brochures - CHANCE® Foundation Solutions Helical Deep Foundation Products Brochure \(BR04146E\)](#)
[Installation Manuals - Holding Capacity Chart - Soil Classification](#)
[Installation Manuals - Holding Capacity Chart - SS200 Anchors](#)
[ISO Certificates - HUS ISO 9001_2015 Cert Jan, 2023](#)
[Literature - Square Shaft Efficient Helical Pile Design \(BR04326E\)](#)
[Literature - New Construction Helical Pile Foundation System \(SF04215E_0419\)](#)
[Sales Drawings - SS200 Anchors \(SA11010019\)](#)
[SDS - MSDS - Galvanized Steel Products](#)
[Video - CHANCE Square Shaft Anchor Tools Selection Process \(VI0651E\)](#)
[Video - CHANCE Square Shaft Anchor Installation \(VI0655E\)](#)