

2" Square Shaft Helical Extension(SS200), 14/14 x 7ft

By Hubbell Power Systems
Catalog # C1100581

SS200, 7' (2134 mm) with 14"/14" helices



*Representative Image

Features

- Finish: Galvanized
- Capacity of helical pile can be determined by measuring installation
- Bolt and nut are assembled to extension at the factory

Application

Helical Anchoring

General

Coating	Galvanized, ASTM A-153
EU RoHS Indicator	No
Number of Helices	2
Strength Note	Ultimate strength ratings apply to properly installed anchors only. Failure to install within 5 ° of alignment with the guy load may significantly lower strength.
Tensile Strength	150000 lb.
Torque Rating	16000 ft-lbs
Type	Anchor Extensions
UPC	096359010036

Dimensions

Anchor Helix Diameter(s)	14 in - 14 in
Length	80.000 in
Weight	148.715 lb

Logistics

Pallet Quantity	12
Standard Package	1

Product Assets

[Brochures - CHANCE® Foundation Solutions Helical Deep Foundation Products Brochure \(BR04146E\)](#)
[ISO Certificates - HUS ISO 9001_2015 Cert Jan, 2023](#)
[Literature - New Construction Helical Pile Foundation System \(SF04215E_0419\)](#)
[Literature - Square Shaft Efficient Helical Pile Design \(BR04326E\)](#)
[Sales Drawings - SS200 Anchors \(SA11010019\)](#)
[SDS - MSDS - Galvanized Steel Products](#)
[Video - CHANCE Square Shaft Anchor Tools Selection Process \(VI0651E\)](#)
[Video - CHANCE Square Shaft Anchor Installation \(VI0655E\)](#)

Related Products

[P0010030P](#)
[P0011445P](#)